



BB019ML9T14TN, 1-Hole Braid, 9" long, 1/4" stud, tinned

By Burndy
Catalog # [BB019ML9T14TN](#)

One-Hole Braid, 19 kcmil, 9", 1/4" stud, tin plated

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Conductor



Conductor Size	#8 AWG
Wire Size	10mm2

Dimensions

Width	0.39 in
Length	9 in
Thickness	0.08 in
Dimension - Stud Size inch	1/4"

General

UPC	621945650527
-----	--------------

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)