



BB024L108 Flexible Copper Braid

By Burndy
Catalog # [BB024L108](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
 - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
 - Braid is especially suited for applications that require flexibility or resistance to vibration
 - Extra fine stranding gives enhanced flexibility
 - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
 - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
 - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	EX
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Length	108 in
--------	--------

General

UPC	781810226698
Material	Copper
UPC 12 Digit	781810226698
UPC 14 Digit GTIN	00781810226698

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2960
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)