



BB024L120 Flexible Copper Braid

By Burndy
Catalog # [BB024L120](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	EX
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Length	120 in
Dimension - L Length Overall mm	3048
Dimension - Length Overall inch	120

General

Material - Ferrules	N
UPC	781810205631
Material	Copper
UPC 12 Digit	781810205631
UPC 14 Digit GTIN	00781810205631

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2220
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)