



BB024L12G30 Flexible Copper Braid

By Burndy
Catalog # BB024L12G30

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	93 A
-----------------	------

Dimensions

Length	12 in
Dimension - L Length Overall	320 mm
Dimension - Length Overall	12.6 inch

General

UPC	781810657775
Material	Copper
UPC 12 Digit	781810657775
UPC 14 Digit GTIN	00781810657775

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)