



# BB024L18G4 Flexible Copper Braid

By Burndy  
Catalog # [BB024L18G4](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | EX |
| Certification - cULus              | No |
| UL Listed                          | No |

Certification - CSA Approved      No

## Configuration

Connector Type      Braid

## Dimensions

|                                 |          |
|---------------------------------|----------|
| Length                          | 18 in    |
| Dimension - L Length Overall mm | 457 mm   |
| Dimension - Length Overall inch | 18.00 in |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | Y              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 1              |
| UPC                                   | 781810140024   |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810140024   |
| UPC 14 Digit GTIN                     | 00781810140024 |

## Product Assets

[Catalog \[English\]](#)