



BB024L24D48G64 Flexible Copper Braid

By Burndy
Catalog # BB024L24D48G64

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	93 A
-----------------	------

Dimensions

Length	24.48 in
Dimension - Width mm	13 mm
Dimension - Width inch	0.5
Dimension - L Length Overall mm	622
Height	0.08 in
Width	0.5 in
Dimension - Length Overall inch	24.48
Dimensions	24.48 in x 0.5 in x 0.08 in

General

UPC	781810646885
Material	Copper
UPC 12 Digit	781810646885
UPC 14 Digit GTIN	00781810646885

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)