



BB024L38G61TN Tinned copper braid

38"x0.50"x0.15"

By Burndy
Catalog # [BB024L38G61TN](#)

Tinned copper braid 38"x0.50"x0.15"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	93 A
-----------------	------

Dimensions

Length	38 in
Dimension - Width mm	13 mm
Dimension - Width inch	0.5
Dimension - L Length Overall mm	965
Height	0.15 in
Width	0.5 in
Dimension - Length Overall inch	38
Dimensions	38 in x 0.5 in x 0.15 in

General

Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810569252
Material	Copper
UPC 12 Digit	781810569252
UPC 14 Digit GTIN	00781810569252

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)