



BB024L42T14 Flexible Copper Braid

By Burndy
Catalog # BB024L42T14

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	UI
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	93 A
-----------------	------

Dimensions

Length	42 in
Dimension - L Length Overall	1067 mm
Dimension - Length Overall	42.00 inch

General

Plated	Y
Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810648339
Material	Copper
UPC 14 Digit GTIN	00781810648339

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)