



BB024L60G79 Cu Braid, Tin, 1-Ferrule, 3/8" Stud, 60: Length

By Burndy
Catalog # [BB024L60G79](#)

Tinned Copper Braid w/Single Ferrule, #8 AWG Equivalent, Stud Hole = 3/8", 60" Overall Length



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Application

Grounding

Dimensions

Package Height	0.000 in
Length	60 in
Thickness	.10 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

UPC	621945524743
Material	Tinned Copper

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4500
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)