



BB024L72G56TN Flexible Copper Braid

By Burndy
Catalog # [BB024L72G56TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	93 A
--------------------------	------

Dimensions

Length	72 in
Dimension - L Length Overall	1829 mm
Dimension - Length Overall	72 inch

General

Plated	Y
Material - Ferrules	Y
UPC	781810550458
Material	Copper
UPC 12 Digit	781810550458
UPC 14 Digit GTIN	00781810550458

Product Assets

[Catalog \[English\]](#)