



BB024L8G18 Tinned copper braid with HYLUG™ Series, 8"x0.48"x0.08"

By Burndy
Catalog # [BB024L8G18](#)

Tinned copper braid with HYLUG™ 8"x0.48"x0.08"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	93 A
-----------------	------

Dimensions

Length	8 in
Dimension - Width mm	12 mm
Dimension - Width inch	0.48
Dimension - L Length Overall mm	203
Height	0.08 in
Width	0.48 in
Dimension - Length Overall inch	8
Dimensions	8 in x 0.48 in x 0.08 in

General

Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810643433
Material	Copper
UPC 12 Digit	781810643433
UPC 14 Digit GTIN	00781810643433

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)



A Hubbell brand