



BB024SS18G63TN, Flexible Stainless Steel Braid, Tin Plated

By Burndy
Catalog # [BB024SS18G63TN](#)

Flexible Stainless Steel Braid, Tin Plated



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
Dimensions	
Package Height	0.000 in
Length	18 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	457
Dimension - Length Overall inch	8
General	
UPC	781810643730
Material	Stainless Steel
UPC 12 Digit	781810643730
UPC 14 Digit GTIN	00781810643730

Logistics

Minimum Pack Quantity	1
Pallet Quantity	12000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)