



BB024SS18T14TN Stainless steel braid with HYLUG™ Series, 18"x0.43"x0.04"

By Burndy
Catalog # [BB024SS18T14TN](#)

Stainless steel braid with HYLUG™ 18"x0.43"x0.04"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Length	18 in
Dimension - Width mm	11 mm
Dimension - Width inch	0.43
Dimension - L Length Overall mm	457
Height	0.04 in
Width	0.43 in
Dimension - Length Overall inch	18
Dimensions	18 in x 0.43 in x 0.04 in

General

Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810643693
Material	Stainless Steel
UPC 12 Digit	781810643693
UPC 14 Digit GTIN	00781810643693

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)