



BB024SSL12LT516, Stainless Steel Flexible Braid

By Burndy
Catalog # [BB024SSL12LT516](#)

Flexible Stainless Steel Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance CM
Status

Configuration

Connector Type	Braid
Dimensions	
Length	12.63 in
Dimension - L Length Overall mm	320.8
Dimension - Length Overall inch	12.63
General	
UPC	781810674819
Material	Stainless Steel
UPC 12 Digit	781810674819
UPC 14 Digit GTIN	00781810674819
Logistics	
Pallet Quantity	4200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)