



BB024SSL6LT38, Stainless Steel Flexible Braid

By Burndy
Catalog # [BB024SSL6LT38](#)

Flexible Stainless Steel Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	6.63 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	168.4
Dimension - Length Overall inch	6.63

General

UPC	781810674826
Material	Stainless Steel
UPC 12 Digit	781810674826
UPC 14 Digit GTIN	00781810674826

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5550
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)