



BB031ML12T14TN, 1-Hole Braid, 12" long, 1/4" stud, tinned

By Burndy
Catalog # [BB031ML12T14TN](#)

One-Hole Braid, 31 kcmil, 12", 1/4" stud, tin plated



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Conductor

Conductor Size	#6 AWG
Wire Size	16mm2

Dimensions

Width	0.59 in
Package Height	0.000 in
Length	12 in
Thickness	0.09 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Stud Size inch	1/4"

General

UPC	621945650398
-----	--------------

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)