



BB038SSL7D87T12, Flexible Stainless Steel Braid

By Burndy
Catalog # [BB038SSL7D87T12](#)

Flexible Stainless Steel Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved No

Configuration

Connector Type Braid

Dimensions

Package Height	0.000 in
Length	7.87 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	200 mm
Dimension - Length Overall	7.8 inch

General

UPC	621945453845
Material	Stainless Steel
UPC 12 Digit	621945453845
UPC 14 Digit GTIN	00621945453845

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalog \[English\]](#)