



# BB048L18LT12 Flexible Copper Braid

By Burndy  
Catalog # [BB048L18LT12](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                              |    |
|------------------------------|----|
| Standards - RoHS Compliance  | CM |
| Status                       |    |
| Certification - CSA Approved | No |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Dimensions

|                              |            |
|------------------------------|------------|
| Package Height               | 0.000 in   |
| Length                       | 18.86 in   |
| Package Weight               | 0.000 lb.  |
| Package Length               | 0.000 in   |
| Package Width                | 0.000 in   |
| Dimension - L Length Overall | 479 mm     |
| Dimension - Length Overall   | 18.86 inch |

## General

|                   |                |
|-------------------|----------------|
| Plated            | Y              |
| UPC               | 781810674963   |
| Material          | Copper         |
| UPC 12 Digit      | 781810674963   |
| UPC 14 Digit GTIN | 00781810674963 |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 4800 |
| Carton Quantity       | 50   |

## Product Assets

[Catalog \[English\]](#)