



BB048L24LT38 Flexible Copper Braid

By Burndy
Catalog # BB048L24LT38

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - RoHS Compliance CM
Status

Configuration

Connector Type Braid

Dimensions

Package Height 0.000 in
Package Weight 0.000 lb.
Package Length 0.000 in
Package Width 0.000 in

General

UPC 781810674949
Material Copper
UPC 12 Digit 781810674949
UPC 14 Digit GTIN 00781810674949

Logistics

Pallet Quantity 3000
Carton Quantity 50

Product Assets

[Catalog \[English\]](#)