



BB048L24T14 Flexible Copper Braid

By Burndy
Catalog # [BB048L24T14](#)

Tinned copper BRAID 24X0.75X0.13.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB048L24T14
Connector Type	Braid
Material	Copper
UPC	621945437661
UPC 14 Digit GTIN	00621945437661

Dimensions

Length	24 in
--------	-------

Electrical Ratings

Current Rating	93 A
----------------	------

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	50
Pallet Quantity	3000

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50007334](#)
- [Specifications - BB048L24T14 Specification Sheet French](#)
- [Specifications - BB048L24T14 Specification Sheet English](#)



A Hubbell brand