



BB048L60G35 Tinned Copper Braid w/Single Ferrule, #3 AWG Equivalent , Stud Hole = 3/8", 60" Overall Length

By Burndy
Catalog # [BB048L60G35](#)



Tinned Copper Braid w/Single Ferrule, #3 AWG Equivalent , Stud Hole = 3/8", 60" Overall Length.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Application

Grounding

General

Catalog Number	BB048L60G35
UPC	621945521322

Dimensions

Length	60 in
Thickness	.13 in

Logistics

Carton Quantity	29
Minimum Pack Quantity	1
Pallet Quantity	1015

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50090707](#)
[Specifications - BB048L60G35](#)



A Hubbell brand