



BB048L6T14 Flexible Copper Braid

By Burndy
Catalog # [BB048L6T14](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
 - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
 - Braid is especially suited for applications that require flexibility or resistance to vibration
 - Extra fine stranding gives enhanced flexibility
 - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
 - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
 - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	93 A
-----------------	------

Rating - Indoor Amperage	150
Rating - Outdoor Amperage	150

Dimensions

Package Height	0.000 in
Length	6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	152 mm
Dimension - N inch	0.5 in
Dimension - Length Overall	6 inch
Dimension - Stud Size inch	1/4

General

Plated	Y
Physical Attribute - Number of Braids	1
UPC	781810552469
Material	Copper
UPC 12 Digit	781810552469
UPC 14 Digit GTIN	00781810552469

Logistics

Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)