



**BB049ML24T38TN, 1-Hole Braid, 24" long,
3/8" stud, tinned**

By Burndy
Catalog # [BB049ML24T38TN](#)

One-Hole Braid, 49 kcmil, 24", 3/8" stud, tin plated



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Conductor

Conductor Size	#4 AWG
Wire Size	25mm2
Dimensions	
Width	0.91 in
Length	24 in
Thickness	0.13 in
Dimension - Stud Size inch	3/8"
General	
UPC	621945650763
Logistics	
Pallet Quantity	1
Carton Quantity	1
Product Assets	
Catalog [English]	