



**BB049ML9T14TN, One-Hole Braid, 9" long,
1/4" stud, tin plated**

By Burndy
Catalog # [BB049ML9T14TN](#)

One-Hole Braid, 49 kcmil, 9", 1/4" stud, tin plated

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Conductor



Conductor Size	#4 AWG
Wire Size	25mm2
Dimensions	
Width	0.91 in
Length	9 in
Thickness	0.13 in
Dimension - Stud Size inch	1/4"
General	
UPC	621945650688
Logistics	
Pallet Quantity	1
Carton Quantity	1
Product Assets	
Catalog [English]	