



**BB059ML18T38TN, 1-Hole Braid, 18" long,
3/8" stud, tinned**

By Burndy
Catalog # [BB059ML18T38TN](#)

One-Hole Braid, 59 kcmil, 18", 3/8" stud, tin plated

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Conductor



Conductor Size	#3 AWG
Wire Size	30mm2
Dimensions	
Width	0.91 in
Length	18 in
Thickness	0.13 in
Dimension - Stud Size inch	3/8"
General	
UPC	621945650800
Logistics	
Pallet Quantity	1
Carton Quantity	1
Product Assets	
Catalog [English]	