



BB059ML24T38TN, One-Hole Braid, 24" long, 3/8" stud, tin plated

By Burndy
Catalog # [BB059ML24T38TN](#)

One-Hole Braid, 59 kcmil, 24", 3/8" stud, tin plated

Features

- Most Burndy braid are UL Listed and CSA Certified
 - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
 - Braid is especially suited for applications that require flexibility or resistance to vibration
 - Extra fine stranding gives enhanced flexibility
 - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
 - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
 - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- www.hubbell.com/config/BRAID

Conductor



Conductor Size	#3 AWG
Wire Size	30mm2
Dimensions	
Width	0.91 in
Length	24 in
Thickness	0.13 in
Dimension - Stud Size inch	3/8"
General	
UPC	621945650817
Logistics	
Pallet Quantity	1
Carton Quantity	1
Product Assets	
Catalog [English]	