



BB059ML9T38TN, One-Hole Braid, 9" long, 3/8" stud, tin plated

By Burndy
Catalog # [BB059ML9T38TN](#)

One-Hole Braid, 59 kcmil, 9", 3/8" stud, tin plated, approx AWG Size #3

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number BB059ML9T38TN
UPC 621945650787



Dimensions

Dimension - Stud Size inch	3/8"
Length	9 in
Thickness	0.13 in
Width	0.91 in

Conductor Related

Conductor Size	#3 AWG
Wire Size	30mm2

Product Assets

- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50121364](#)
- [Specifications - BB059ML9T38TN](#)