



BB067L17G9 Flexible Copper Braid

By Burndy
Catalog # BB067L17G9

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Length	17 in
Dimension - Width mm	21 mm
Dimension - Width inch	0.83
Dimension - L Length Overall mm	432
Height	0.17 in
Width	0.83 in
Dimension - Length Overall inch	17
Dimensions	17 in x 0.83 in x 0.17 in

General

Material - Ferrules	Copper
UPC	781810566824
Material	Copper
UPC 12 Digit	781810566824
UPC 14 Digit GTIN	00781810566824

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)