



# BB067L300 Flexible Copper Braid

By Burndy  
Catalog # [BB067L300](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                              |    |
|------------------------------|----|
| Standards - RoHS Compliance  | CM |
| Status                       |    |
| Certification - CSA Approved | No |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Dimensions

|                                 |        |
|---------------------------------|--------|
| Length                          | 300 in |
| Dimension - L Length Overall mm | 7620   |
| Dimension - Length Overall inch | 300    |

## General

|                   |                |
|-------------------|----------------|
| Plated            | Y              |
| UPC               | 781810675236   |
| Material          | Copper         |
| UPC 12 Digit      | 781810675236   |
| UPC 14 Digit GTIN | 00781810675236 |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[Catalog \[English\]](#)