



BB067L9T14 Flexible Copper Braid

By Burndy
Catalog # BB067L9T14

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	93 A
Rating - Indoor Amperage	180
Rating - Outdoor Amperage	180

Dimensions

Length	9 in
Dimension - L Length Overall mm	229 mm
Dimension - N inch	0.5 in
Dimension - Length Overall inch	9.00 in
Dimension - Stud Size inch	1/4

General

Plated	Y
Physical Attribute - Number of Braids	1
UPC	781810552490
Material	Copper
UPC 12 Digit	781810552490
UPC 14 Digit GTIN	00781810552490

Logistics

Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)