



BB077L396 Flexible Copper Braid

By Burndy
Catalog # [BB077L396](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
Certification - CSA Approved	No
UL Listed	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Dimension - L Length Overall mm	10058 mm
Length	396 in
Dimension - Length Overall inch	396 in

General

Material - Ferrules	Y
Plated	Y
UPC 12 Digit	781810223109
UPC 14 Digit GTIN	00781810223109
Material	Copper
UPC	781810223109

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)