



BB099ML12T58TN, One-Hole Braid, 12" long, 5/8" stud, tin plated

By Burndy

Catalog # [BB099ML12T58TN](#)

One-Hole Braid, 99 kcmil, 12", 5/8" stud, tin plated



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)

- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Dimensions

Length 12 in

General

UPC 621945650930

Product Assets

[Catalog \[English\]](#)



A Hubbell brand