



**BB099ML9T38TN, 1-Hole Braid, 9" long,
3/8" stud, Tinned**

By Burndy
Catalog # [BB099ML9T38TN](#)

One-Hole Braid, 99 kcmil, 9", 3/8" stud, tin plated



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Conductor

Conductor Size	#1 AWG
Wire Size	50mm2

Dimensions

Width	1.1 in
Package Height	0.000 in
Length	9 in
Thickness	0.14 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Stud Size inch	3/8"

General

UPC	621945650886
-----	--------------

Logistics

Pallet Quantity	1
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)