



# BB100L12D81M16TN Flexible Copper Braid, Tin Plated Ferrules

By Burndy  
Catalog # [BB100L12D81M16TN](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                              |     |
|------------------------------|-----|
| UL Listed                    | Yes |
| Certification - CSA Approved | Yes |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Dimensions

|                              |           |
|------------------------------|-----------|
| Package Height               | 0.000 in  |
| Length                       | 12.81 in  |
| Package Weight               | 0.000 lb. |
| Package Length               | 0.000 in  |
| Package Width                | 0.000 in  |
| Dimension - Length Overall   | 12.81 in  |
| inch                         |           |
| Dimension - L Length Overall | 325 mm    |
| mm                           |           |

## General

|                     |              |
|---------------------|--------------|
| Plated              | Y            |
| UPC                 | 621945473126 |
| Material - Ferrules | Y            |
| Material            | Copper       |

## Logistics

|                 |   |
|-----------------|---|
| Pallet Quantity | 1 |
| Carton Quantity | 1 |

## Product Assets

[Catalog \[English\]](#)