



BB100L142D73G21TN Flexible Copper Braid

By Burndy
Catalog # [BB100L142D73G21TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	300 A
-----------------	-------

Dimensions

Length	142.73 in
Dimension - L Length Overall	3600 mm
mm	
Dimension - Length Overall	141.73 in
inch	

General

Plated	Y
Material - Ferrules	Y
UPC	621945434523
Material	Copper
UPC 12 Digit	621945434523
UPC 14 Digit GTIN	00621945434523

Logistics

Minimum Pack Quantity	12
Pallet Quantity	525
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)