



BB100L145D32G15TN Flexible Copper Braid

By Burndy
Catalog # [BB100L145D32G15TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	290 A
-----------------	-------

Dimensions

Length	145.32 in
Dimension - L Length Overall	3691 mm
mm	
Dimension - Length Overall	145.32 in
inch	

General

Plated	Y
Material - Ferrules	Y
UPC	781810508299
Material	Copper
UPC 12 Digit	781810508299
UPC 14 Digit GTIN	00781810508299

Product Assets

[Catalog \[English\]](#)