



BB100L20D69G21TN Flexible Copper Braid

By Burndy
Catalog # [BB100L20D69G21TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
 - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
 - Braid is especially suited for applications that require flexibility or resistance to vibration
 - Extra fine stranding gives enhanced flexibility
 - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
 - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
 - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	300 A
-----------------	-------

Dimensions

Package Height	0.000 in
Length	20.69 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	500 mm
Dimension - Length Overall	19.69 inch

General

Plated	Y
Material - Ferrules	Y
UPC	621945443556
Material	Copper
UPC 12 Digit	621945443556
UPC 14 Digit GTIN	00621945443556

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3600
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)