



BB100L24D60G21TN Flexible Copper Braid

By Burndy
Catalog # [BB100L24D60G21TN](#)



Tin Plated Copper Braid 23.60 inches long.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB100L24D60G21TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Plated	Y
UPC	781810649428
UPC 14 Digit GTIN	00781810649428

Dimensions

Dimension - L Length Overall	599 mm
Dimension - Length Overall	23.6 in
Length	24.6 in

Electrical Ratings

Amperage Rating	300 A
-----------------	-------

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50002016](#)
[Specifications - BB100L24D60G21TN](#)



A Hubbell brand