



BB100L26D50G15TN Flexible Copper Braid

By Burndy
Catalog # [BB100L26D50G15TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
UL Listed	No

Certification - CSA Approved No

Configuration

Connector Type Braid

Dimensions

Length	26.5 in
Dimension - L Length Overall	673 mm
mm	
Dimension - Length Overall	26.50 in
inch	

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of	1
Braids	
UPC	781810491485
Material	Copper
UPC 12 Digit	781810491485
UPC 14 Digit GTIN	00781810491485

Product Assets

[Catalog \[English\]](#)