



BB100L30D53G21TN Flexible Copper Braid

By Burndy
Catalog # [BB100L30D53G21TN](#)

Tin Plated Copper Braid 29.53 inches long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB100L30D53G21TN
Connector Type	Braid
Material	Copper
UPC	621945452725
UPC 14 Digit GTIN	00621945452725

Dimensions

Dimension - L Length Overall	750 mm
Dimension - Length Overall	29.53 in
Length	30.53 in

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	5
Pallet Quantity	525

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50002016](#)
- [Specifications - BB100L30D53G21TN](#)



A Hubbell brand