



BB100L30N Flexible Copper Braid

By Burndy

Catalog # [BB100L30N](#)

Tin Plated Copper Braid 30 inches long.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BB100L30N
Material	Copper
UPC	781810510469
UPC 14 Digit GTIN	00781810510469

Dimensions

Length	30 in
--------	-------

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1
Minimum Pack Quantity	25

Product Assets

[3D Models - BB100L30N_MODEL-IGES](#)
[3D Models - BB100L30N_MODEL-STEP](#)
[3D Models - BB100L30N_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30008316](#)
[Specifications - BB100L30N](#)



A Hubbell brand