



BB100L36N Flexible Copper Braid

By Burndy
Catalog # BB100L36N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
Dimensions	
Package Height	0.000 in
Length	36 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	916 mm
Dimension - Length Overall inch	36.00 in
General	
UPC	781810512838
Material	Copper
UPC 12 Digit	781810512838
UPC 14 Digit GTIN	00781810512838
Logistics	
Minimum Pack Quantity	20
Pallet Quantity	1
Carton Quantity	1
Product Assets	
Catalog [English]	