



BB100L40D36G15TN Flexible Copper Braid

By Burndy
Catalog # [BB100L40D36G15TN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
 - Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
 - Braid is especially suited for applications that require flexibility or resistance to vibration
 - Extra fine stranding gives enhanced flexibility
 - Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
 - Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
 - For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
- www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	

Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Length	40.36 in
Dimension - L Length Overall	1025 mm
mm	
Dimension - Length Overall	40.36 in
inch	

General

UPC	781810508343
Material	Copper
UPC 12 Digit	781810508343
UPC 14 Digit GTIN	00781810508343

Product Assets

[Catalog \[English\]](#)