



BB100L4800 Flexible Copper Braid

By Burndy
Catalog # [BB100L4800](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
Current	
Amperage Rating	290 A
Dimensions	
Length	4800 in
Dimension - L Length Overall	10160 mm
Dimension - Length Overall	400 in
inch	
Thickness - Pad	0.100 in
General	
UPC	781810674093
Material	Copper
UPC 14 Digit GTIN	00781810674093

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)