



BB100LG10KIT Braid kit

By Burndy
Catalog # BB100LG10KIT

Braid kit



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - ETL No

Certification - UL Recognized No
Standards - RoHS Compliance EX
Status
Certification - cULus No
UL Listed No
Certification - CSA Approved No

Configuration

Connector Type Braid

General

UPC 781810360897
Material Copper
UPC 12 Digit 781810360897
UPC 14 Digit GTIN 00781810360897

Product Assets

[Catalog \[English\]](#)