



**BB139ML12T38TN, 1-Hole Braid, 12" long,  
3/8" stud, Tinned**

By Burndy  
Catalog # [BB139ML12T38TN](#)

One-Hole Braid, 139kcmil, 12", 3/8" stud, tin plated



**Features**

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

**Conductor**

|                |         |
|----------------|---------|
| Conductor Size | 2/0 AWG |
| Wire Size      | 70mm2   |

**Dimensions**

|                            |           |
|----------------------------|-----------|
| Width                      | 1.18 in   |
| Package Height             | 0.000 in  |
| Length                     | 12 in     |
| Thickness                  | 0.16 in   |
| Package Weight             | 0.000 lb. |
| Package Length             | 0.000 in  |
| Package Width              | 0.000 in  |
| Dimension - Stud Size inch | 3/8"      |

**General**

|     |              |
|-----|--------------|
| UPC | 621945650961 |
|-----|--------------|

**Logistics**

|                 |     |
|-----------------|-----|
| Pallet Quantity | 900 |
| Carton Quantity | 25  |

**Product Assets**

[Catalog \[English\]](#)