



# BB154L36 Flexible Copper Braid

By Burndy  
Catalog # [BB154L36](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

Standards - RoHS Compliance    NC  
Status

## Configuration

Connector Type                      Braid

## Dimensions

Length                                      36 in  
Dimension - L Length Overall        914 mm  
mm  
Dimension - Length Overall            36 in  
inch

## General

UPC                                          781810444504  
Material                                    Copper  
UPC 12 Digit                              781810444504  
UPC 14 Digit GTIN                      00781810444504

## Product Assets

[Catalog \[English\]](#)