



BB154L7800 Flexible Copper Braid

By Burndy
Catalog # [BB154L7800](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No

Certification - CSA Approved No

Configuration

Connector Type Braid

Dimensions

Length	7800 in
Dimension - L Length Overall	198120 mm
mm	
Dimension - Length Overall	7800 in
inch	

General

UPC	781810202753
Material	Copper
UPC 12 Digit	781810202753
UPC 14 Digit GTIN	00781810202753

Logistics

Minimum Pack Quantity 650

Product Assets

[Catalog \[English\]](#)