



**BB197ML12T12TN, One-Hole Braid, 12" long, 1/2" stud, tin plated**

By Burndy  
Catalog # [BB197ML12T12TN](#)

One-Hole Braid, 197 kcmil, 12", 1/2" stud, tin plated



**Features**

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

**Conductor**

|                |         |
|----------------|---------|
| Conductor Size | 3/0 AWG |
| Wire Size      | 100mm2  |

**Dimensions**

|                            |           |
|----------------------------|-----------|
| Width                      | 1.57 in   |
| Package Height             | 0.000 in  |
| Length                     | 12 in     |
| Thickness                  | 0.19 in   |
| Package Weight             | 0.000 lb. |
| Package Length             | 0.000 in  |
| Package Width              | 0.000 in  |
| Dimension - Stud Size inch | 1/2"      |

**General**

|     |              |
|-----|--------------|
| UPC | 621945651050 |
|-----|--------------|

**Logistics**

|                 |      |
|-----------------|------|
| Pallet Quantity | 1800 |
| Carton Quantity | 50   |

**Product Assets**

[Catalog \[English\]](#)