



BB300L120 Flexible Copper Braid

By Burndy
Catalog # [BB300L120](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved	No
UL Listed	No
Certification - ETL	No

Standards - RoHS Compliance EX
Status

Dimensions

Dimension - L Length Overall	3048 mm
mm	
Dimension - Length Overall	120 in
inch	
Length	120 in

General

UPC	781810198889
-----	--------------

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)